AIKUCAM

NANO1-4K Data Sheet

NANO1-4K

Mini Action Camera

Overview

NANO1-4K features a high-performance CMOS 1/2.49" image sensor that can capture photos of up to 12 MP and video of up to 4K@60FPS.The pixel size is 1.404 μ m x 1.404 μ m. In 4-cell mode , NANO1-4K provides 4 times light sensitivity than a standard camera, resulting in imaging with brigher details in low-light situations.Ehanced by WDR, the dynamic range is greatly improved.

Photos





Specification

General

Size: 36×36×27 mm Waterproof: IP64 Microphone: 1 pcs Weight: 60 g Camera Image Sensor: 1/2.49 inch CMOS FOV: 143° Aperture: f/2.4 Equivalent Focal Length: 17 mm Focus Range: 0.5 m to ∞ ISO Range: 100-3200 Photo: 1/8000 to 16 s Shutter Speed: Video: 1/8000 s to the limit of frames per second 4672×2628 Max Photo Resolution: Digital Zoom: 4X Slow Motion: Yes Single Photo: 12 MP Countdown: Off/3/5/7 seconds 4.5K (16:9): 4512×2512 @ 15fps 4K (16:9): 3840×2160 @ 24/25/30/48/50/60fps 2256×1256 @ 24/25/30/48/50/60fps Regular Video: 2.2K (16:9): 1080p (16:9): 1920×1080 @ 24/25/30/48/50/60/100/120fps 720P(16:9): 1280×720 @ 240fps 4K: 2x (60fps) Slow Motion Video: 1080p: 4x (120fps) 720p: 8x (240fps) Timelapse: Timelapse Resolution: 4.5K/4K/2.2K/1080p/720P 1/2/3/4/5/6/7/8/10/13/15/20/25/30/40/60 seconds Timelapse Intervals: Timelapse Duration: $1/3/5/10/20/30 \text{ minutes}, 1/2/3/5 \text{ hours}, \infty$ Stabilization: (EIS is not supported in slow motion and timelapse mode.)

Max Video Bitrate: 100 Mbps

Supported File Formats: FAT32

Photo Format: JPEG

Video Format: MP4 (H.264)

Audio Output: 48 kHz; AAC

Supported Storage Card Type: MicroSD (Storage capacity of up to 512GB)

Samsung EVO 128GB UHS-I Speed Grade 3 microSDHC

Samsung EVO Plus 128GB UHS-I Speed Grade 3 microSDXC

SanDisk Extreme 64GB V30 A2 UHS-I Speed Grade 3 microSDXC

SanDisk Extreme Pro 32GB UHS-I Speed Grade 3 microSDXC

Recommended MicroSD:

SanDisk Extreme 16GB UHS-I Speed Grade 3 microSDXC

Lexar 1066x 64GB UHS-I Speed Grade 3 microSDHC

Kingston Canvas React Plus 64GB UHS-II Speed Grade 3 microSD Kingston Canvas Go!Plus 64GB UHS-I Speed Grade 3 microSD

Battery

Type: LiPo 2S

Capacity: 500 mAh
Energy: 1.85 Wh

Voltage: 4.2 V

Operating Temperature: -10°C to 40°C

Working Temperature: -10°C to 40°C

Operating Time: 70 minutes in 4K

120 minutes in low power mode

Tested in a laboratory environment while recording 1080p/30fps (Power

Reserve) video with electronic image stabilization disabled. This figure

should be used for reference only

Connection


Wi-Fi Frequency Range: 2.400-2.4835 GHz

Wi-Fi Protocol: 802.11 b/g/n

Descriptions of Port Functions

The USB port of NANO1-4K supports charging with 5V of electricity and audio input from an optional external mic. You can connect NANO1-12M to a PC with a USB cable and click the " button to turn it into a webcam. From there, you can take photos and record videos with the built-in camera features in Windows 10. A MicroSD card with preloaded configuration file can be put into the card slot to override the settings of the camera. With the magnetic design, the camera can be attached to a magnetic mount (which must be purchased separately).

Product Diagram





Button:

Press it to enter photo mode. It will automatically shut down after the photo is taken.

Press and hold it for 2 seconds to power on the camera and enter video mode by default.

Press and hold it for 8 seconds to restart the camera (during downtime).

In video mode, press it to switch to photo mode and take one photo.

Button:

Press it to immediately starting shooting video. Press it again to stop recording and power off the camera.

Press it and hold it for 3 seconds tor power on the camera and enter the video mode by default.

When the camera is powered on, press it to record video. Press it again to stop recording.

When the camera is powered on, press and hold it for 3 seconds to turn on or off the Wi-Fi.

WiFi name "NANO****" WiFi password "12345678"

Descriptions of status LED

Buttons LED	LED status	Descriptions	Camera status
0		Solid red	Charging
		Solid green	Charging completed
•		Solid red	Video mode
		Blinking red	Recording
		Solid green	Photo mode
		Blinking green	Taking photos
		Blinking blue	WiFi on
		Solid blue	WiFi connected
		Blinking yellow	No SD card

Description of vibiration alarm

Buttons	Camera status	Operation	Vibration frequency
•	Powering on	Press & hold it 2 seconds	
	Taking a photo	Press quickly	
	Restarting	Press & hold it for 8 secons (during downtime)	
	Powering off	Press & hold it for 3 seconds	
•	Powering on	Press & hold it for 2 seconds	
	Recording	Press quickly	
	Stop recording	Press quickly	
	WiFi on	Press & hold it for 3 seconds	
	WiFi off	Press & hold it for 3 seconds	

AiKUCAM 3/3 www.aikucam.com